

Product Data Sheet

AkzoNobel Powder Coatings

Interpon D3020 Matt (25)

Product Description

Interpon D3020 is a series of hyperdurable powder coatings designed to meet the most demanding architectural specification requirements in the world. AkzoNobel's Fluorocarbon technology uses innovative fluorocarbon polymer chemistry that is designed to provide maximum gloss and color retention in service.

Interpon D3020 is also designed to provide excellent cosmetic and functional protection whilst exploiting the recognized benefits of powder coatings complying with QUALICOAT Class 3.

Interpon D3020 is awarded the prestigious Qualicoat Class 3 approval for hyperdurable architectural powder coatings and conforms to the requirements of AAMA-2605, EN12206 and GSB Premium specifications.

Qualicoat Licence number: P-1175 (Turkey)

GSB Licence number: 246b

Powder Properties	Chemical type	Fluoropolymer	
	Appearance	Smooth Matt	
	Gloss level	20 - 30 gloss units	
	Particle Size	Suitable for electrostatic spray	
	Specific gravity	1.2-1.7g/cm ³ depending on colour.	
	Storage	Dry, cool conditions (open boxes must be resealed)	
	Shelf life	6 months below 25°C peak temperature	
	Curing schedule (at object temperature)	20-35 minutes at 190°C 15-25 minutes at 200°C	
Mechanical Tests	Flexibility	ISO 1519 (cylindrical Mandrel)	Pass Qualicoat class 3 requirements
	Adhesion	ISO 2409 (2mm Crosshatch)	Pass Gt0
	Erichsen cupping	ISO1520	Pass Qualicoat class 3 requirements
	Impact resistance	ISO 6272	Pass Qualicoat class 3 requirements
	Hardness	ISO 2815	> 80
Environmental and Durability Tests	Acetic Acid Salt Spray	ISO 9227	<16 mm ² corrosion/10cm (2000 hrs)
	Constant Humidity	ISO 6270	No blistering, creep <1mm (2000 hrs)
	Sulphur Dioxide	ISO 3231	Pass 24 cycles– no blistering, loss of gloss or discoloration
	Permeability	Pressure Cooker EN12206-2004	Pass 1 hour, no blistering

Interpon D3020 Matt (25)



			acid, alkalis and oils at normal			
	Mortar Resistance	EN12206-2004	temperatures. No effect after 24 hours			
	Accelerated	ISO16474-2 (2000 hrs)	>90% Gloss retention			
	Weathering	100104742 (20001113)	Color change: not greater than 50% of the limits prescribed in Qualicoat Specifications			
	Exterior Durability	ISO 2810	Meets qualicoat class 3 requirements after 10 years Florida			
			Meets AAMA 2605 requirements after 10 years Florida			
Test Conditions		Testing has been determined under laboratory conditions using the following application properties and is for guidance only.				
	Substrate	Aluminum (0.5-0.8 mm Al Mg1)				
	Pretreatment	Chrome free Qualicoat/GSB approved pretreatment				
	Film thickness	50-80 microns (ISO 2360)				
	Cure schedule	20 minutes at 200° C (object temperature)				
	Actual film performance will depend on the individiual circumstances in which the product is used.					
Pre-treatment	Interpon D3020 in accordance Aluminium components suitable chrome-free pr	ordance with the Interpon D A should receive a full multi-sta e-treatment or suitable pre-an	pproved Applicator Manual Ige chromate conversion coating o odising to clean and condition the			
Pre-treatment	Interpon D3020 in accordance Aluminium components suitable chrome-free pr	ordance with the Interpon D A should receive a full multi-sta	ige chromate conversion coating or odising to clean and condition the			
Pre-treatment Application	Interpon D3020 in accordance Aluminium components suitable chrome-free productions substrate. Detailed advious Interpon D3020 Mat production equipment. Unused powerupment and recycles.	ordance with the Interpon D A should receive a full multi-state-treatment or suitable pre-antice should be sought from the bowders can be applied by mar	pproved Applicator Manual. age chromate conversion coating of odising to clean and condition the pre-treatment supplier. anual or automatic electrostatic spratum maximum of 20% using suitable consult AkzoNobel for further			
	Interpon D3020 in accordance Aluminium components suitable chrome-free productions and substrate. Detailed advisor Interpon D3020 Mat production production and recycles details as to the correct All powders can show sunavoidable. While Akz cannot be guaranteed.	erdance with the Interpon D A should receive a full multi-state-treatment or suitable pre-antice should be sought from the owders can be applied by marked can be reclaimed up to a through the system. Please mixing ratio for virgin/reclaims and color differences from be conobel take every precaution Applicators and fabricators are	pproved Applicator Manual. age chromate conversion coating of odising to clean and condition the pre-treatment supplier. anual or automatic electrostatic spratum maximum of 20% using suitable consult AkzoNobel for further			
	Interpon D3020 in accordance Aluminium components suitable chrome-free prosubstrate. Detailed advisorable interpon D3020 Mat prosubstrate. Unused power equipment. Unused power equipment and recycled details as to the correct All powders can show sunavoidable. While Akz cannot be guaranteed. parts that will be assempowders. Bonded metallic product (more stable) but attent effect" and changes in a recycled powders should a suitable of the components.	ordance with the Interpon D A should receive a full multi-state-treatment or suitable pre-antice should be sought from the owders can be applied by marked can be reclaimed up to a district through the system. Please mixing ratio for virgin/reclaim small color differences from base on Nobel take every precaution Applicators and fabricators and bled together. Differences are stated to the paid to line aspect after recycling. A constitution of the should still be paid to line aspect after recycling.	pproved Applicator Manual. age chromate conversion coating of odising to clean and condition the pre-treatment supplier. The pre-treatment supplier of the			
	Interpon D3020 in accordance Aluminium components suitable chrome-free prosubstrate. Detailed advisorable interpon D3020 Mat prosubstrate. Unused power equipment. Unused power equipment and recycled details as to the correct All powders can show sunavoidable. While Akz cannot be guaranteed. parts that will be assempowders. Bonded metallic product (more stable) but attent effect" and changes in a recycled powders shoul For more information, it	ordance with the Interpon D A should receive a full multi-state-treatment or suitable pre-antice should be sought from the owders can be applied by marked can be reclaimed up to a district through the system. Please mixing ratio for virgin/reclaims and color differences from backnowled take every precaution Applicators and fabricators are all together. Differences are stated together application profice in should still be paid to line aspect after recycling. A constituted to the coater in order to the should still be paid to line aspect after recycling. A constitute of the coater in order to the should still be coater in order to the coater to the coater in order to the coater to the co	pproved Applicator Manual. age chromate conversion coating of odising to clean and condition the pre-treatment supplier. Inual or automatic electrostatic sprain maximum of 20% using suitable consult AkzoNobel for further powder. In actch to batch, this is normal and to minimize visible differences, the eadvised to use a single batch for emore likely with special effect operties than blended products settings in order to avoid "marble ant ratio between virgin and der to achieve a consistent effect. allic Applications Guidelines.			



	Interpon D3020 is based on fluorocarbon polymer chemistry hence corona application is recommended to get proper charging. Please contact Akzo Nobel or consult with your equipment supplier for alternatives.		
Post Application	For specific advice on the suitability of post coating processes such as bending or the use of sealants, adhesives, thermal break, cleaning etc. Please consult AkzoNobel.		
Maintenance	For specific advice on Cleaning and Maintenance, please consult the <i>Interpon D series Cleaning and Maintenance Guidelines</i> available from AkzoNobel.		
Safety Precautions	Interpon D3020 series contains caprolactam. When using, do not eat, drink or smoke. Do not breathe in the dust. In case of insufficient ventilation, wear suitable respiratory equipment.		
	For further information, please consult the Material Safety Datasheet (MSDS) available from AkzoNobel.		
Disclaimer	IMPORTANT NOTE: The information in this data sheet is not intended to be exhaustive and is based on the present state of our knowledge and on current laws: any person using the product for any purpose other than that specifically recommended in the technical data sheet without first obtaining written confirmation from us as to the suitability of the product for the intended purpose does so at his own risk. It is always the responsibility of the user to take all necessary steps to fulfil the demands set out in the local rules and legislation. Always read the Material Data Sheet and the Technical Data Sheet for this product if available. All advice we give or any statement made about the product by us (whether in this data sheet or otherwise) is correct to the best of our knowledge but we have no control over the quality or the condition of the substrate or the many factors affecting the use and application of the product.		
	Therefore, unless we specifically agree in writing otherwise, we do not accept any liability whatsoever for the performance of the product or for any loss or damage arising out of the use of the product. All products supplied and technical advices given are subject to our standard terms and conditions of sale. You should request a copy of this document and review it carefully. The information contained in this data sheet is subject to modification from time to time in the light of experience and our policy of continuous development. It is the user's responsibility to verify that this data sheet is current prior to using the product.		
	Brand names mentioned in this data sheet are trademarks of or are licensed to AkzoNobel		

http://www.interpon.com/contact-us/

 $\label{localized Copyright @ 2015 Akzo Nobel Powder Coatings Ltd.} Interpon is a registered trademark of AkzoNobel Interpon D3020 Matt (25) - Issue 14$

Last Revision Date: 03/03/2017